


TXP-2 Tap Out Actuator




The implementation of Precimeter Technology provides many advantages

- Quality improvements
- Increased productivity
- Documentation of the process
- Raw material savings
- Energy savings
- Better use of manpower

TXP-2 Tap Out Actuator



This small and compact Tap Out Actuator is primarily used for control of metal flow through a pin plug valve in head box applications.



Technical Specifications

Stroke:	50 mm (2")
Positioning:	Stepper motor
Closing force:	100 Kg (220 lbs)
Ambient temperature:	175 °C (350 °F)
Power requirement:	18-32 VDC / 1.2 mA
Analog input:	4-20 mA
Analog output:	4-20 mA feed back position signal
Digital inputs:	Analog enable / move pin according to 4-20mA. Calibrate to closed or open position
Digital output:	Temperature alarm 65 °C (150 °F)

TXP-2 includes one heavy duty connector and mating control box.

Contact Precimeter Group

EASTERN AND CENTRAL EUROPE DIE CASTING AND EM PUMPS

Carli Precimeter GmbH
Kirberg 5/ 51674 Wiehl/ DE
Phone: +49-2262-701624 Fax: +49-2262-701625

WESTERN EUROPE, MIDDLE EAST, AFRICA, ASIA AND AUSTRALIA

Precimeter Control AB
Östra Hamnen 7/ SE-475 42 Hönö/ SE
Phone: +46-31-764 55 20 Fax: +46-31-764 55 29
www.precimeter.com
info@precimeter.com

NORTH, CENTRAL AND SOUTH AMERICA

Sentech Precimeter Inc.
2215 S. 48th Str. #C / Tempe, AZ 85282/ U.S.A
Phone: +1 (480) 829-1923 Fax: +1 (480) 894-5546

Local Precimeter Contact